

Miele W1 Program Guide

| GENERAL (Options) | PRE-WASH → (Options) | MAIN WASH → Level | Temperature | Rhythm | (Options) | RINSE → Level | Rinses (Options) | SPIN → Speed | END PROGRAM (Options) | TIME |
|---|-------------------------|----------------------|--|-----------|-----------|------------------|------------------|--|--------------------------|-------------|
| Normal – Cottons, linens, and mixed loads of both. DOE/CSA energy/water-efficient program. Full load 17.6 lb/8 kg | | | | | | | | | | 1:26 |
| (SingleWash) (Eco) (Extra Gentle) (AllergoWash) | (Pre-wash) (Soak) | Low | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Intensive | (Bleach) | Medium | 2–3 (ExtraRinse) | Max/1600 rpm Rinse Hold No Spin | | |
| Sanitize – Cottons or linens with special hygiene requirements. Full load 17.6 lb/8 kg | | | | | | | | | | 2:28 |
| (SingleWash) (Eco) (Extra Gentle) (AllergoWash) | (Pre-wash) (Soak) | Low | Sanitize/170°F/75°C | Intensive | (Bleach) | Medium | 2 (ExtraRinse) | Max/1600 rpm High/1200 rpm Rinse Hold No Spin | (SoftSteam) | Anti-Crease |
| Wrinkle-free – Wrinkle-free cottons, synthetics, or mixed-fiber fabric. A Permanent Press program. Half load 8.8 lb/4 kg | | | | | | | | | | 1:39 |
| (SingleWash) (Eco) (ExtraGentle) (AllergoWash) | (Pre-wash) (Soak) | Low | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Normal | (Bleach) | High | 2–4 (ExtraRinse) | High/1200 rpm (SoftSteam) Med/800 rpm Slow/600 rpm Rinse Hold No Spin | (SoftSteam) | Anti-Crease |
| Delicates – Fine synthetic fabrics. Small load 6.6 lb/3 kg | | | | | | | | | | 1:04 |
| (SingleWash) (Eco) (ExtraGentle) (AllergoWash) | (Pre-wash) (Soak) | Low | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Sensitive | | High | 2–4 (ExtraRinse) | Med/800 rpm (SoftSteam) Slow/600 rpm Rinse Hold No Spin | (SoftSteam) | Anti-Crease |
| QuickIntenseWash – Lightly/moderately dirty fabrics suitable for the Normal program. Full load 11 lb/5 kg | | | | | | | | | | 0:49 |
| | | Low | Hot+/140°F/60°C Warm+/105°F/40°C | Intensive | | Medium | 2 (ExtraRinse) | Max/1600 rpm High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | (SoftSteam) | Anti-Crease |

| GENERAL (Options) | PRE-WASH → (Options) | MAIN WASH → Level Temperature | | Rhythm | (Options) | RINSE → Level | Rinses (Options) | | SPIN → Speed | END PROGRAM (Options) | TIME | |
|--|-------------------------|-------------------------------------|--|--|-----------|------------------|------------------|--------------|--|--|------------------------------|------|
| Express – <i>Lightly dirty cottons</i> . Half load 7.7 lb/3.5 kg | | | | | | | | | | | | |
| | | Low | Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Intensive | | Low | 2 | | High/1200 rpm Med/800 rpm Slow/600 rpm No Spin | Anti-Crease | 0:30 | |
| Handwash – <i>Fine textiles suitable for hand washing</i> . Small load 4.4 lb/2 kg | | | | | | | | | | | | |
| (SingleWash) | | High | Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Handwash | | High | 2 | | High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | | 0:39 | |
| Towels – <i>Cotton or linen towels</i> . Full load 11 lb/5 kg | | | | | | | | | | | | |
| (Eco) | (Pre-wash) | Low | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Intensive | | Medium | 2–5 | (ExtraRinse) | Max/1600 rpm High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | Anti-Crease | 0:46 | |
| Extra White – <i>White cottons or linens</i> . Full load 17.6 lb/8 kg | | | | | | | | | | | | |
| (SingleWash) (Eco) (ExtraGentle) (AllergoWash) | (Pre-wash) | (Soak) | Low | Hot+/140°F/60°C | Intensive | (Bleach) | Medium | 2–5 | (ExtraRinse) | Max/1600 rpm High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | (SoftSteam) Anti-Crease | 1:52 |
| Dress Shirts – <i>Cotton, linen, or synthetic shirts or blouses</i> . Small load 4.4 lb/2 kg | | | | | | | | | | | | |
| (SingleWash) (Eco) (ExtraGentle) (AllergoWash) | (Pre-wash) | (Soak) | Low | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Sensitive | (Bleach) | High | 3–4 | (ExtraRinse) | Med/800 rpm Slow/600 rpm Rinse Hold | SoftSteam Anti-Crease | 1:36 |

| GENERAL (Options) | PRE-WASH → (Options) | MAIN WASH → Level Temperature | | Rhythm | (Options) | RINSE → Level | Rinses (Options) | SPIN → Speed | END PROGRAM (Options) | TIME |
|--|-------------------------|----------------------------------|--------|--|-----------|------------------|------------------|--|--------------------------|------|
| Denim/Jeans – <i>Cotton denim</i> . Small load 4.4 lb/2 kg | | | | | | | | | | 1:31 |
| (SingleWash) (Eco) (ExtraGentle) (AllergoWash) | (Pre-wash) | (Soak) | Medium | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Normal | High | 2–4 (ExtraRinse) | Med/800 rpm Slow/600 rpm Rinse Hold No Spin | (SoftSteam) Anti-Crease | |
| Darks – <i>Black or dark-colored cottons, linens, or synthetics</i> . Small load 4.4 lb/2 kg | | | | | | | | | | 1:31 |
| (SingleWash) (Eco) (ExtraGentle) (AllergoWash) | (Pre-wash) | (Soak) | Medium | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Normal | High | 3–5 (ExtraRinse) | High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | (SoftSteam) Anti-Crease | |
| Woolens – <i>Wool or wool blends</i> . Small load 4.4 lb/2 kg | | | | | | | | | | 0:39 |
| (SingleWash) | | | High | Warm/85°F/30°C Cold/Tap | Handwash | High | 2 | High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | | |
| Silks – <i>Silk, lace, and other hand-washables</i> . Very small load 2.2 lb/1 kg | | | | | | | | | | 0:37 |
| (SingleWash) | | | High | Warm/85°F/30°C Cold/Tap | Handwash | High | 2 | Slow/600 rpm Rinse Hold No Spin | | |
| Outdoor – <i>Synthetic membrane fabrics, e.g. Gore-Tex</i> . Small load 5.5 lb/2.5 kg | | | | | | | | | | 1:13 |
| (Eco) | (Pre-wash) | (Soak) | High | Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Sensitive | High | 3–4 (ExtraRinse) | Med/800 rpm Slow/600 rpm Rinse Hold No Spin | Anti-Crease | |

| GENERAL (Options) | PRE-WASH → (Options) | MAIN WASH → Level | Temperature | Rhythm | (Options) | RINSE → Level | Rinses (Options) | SPIN → Speed | END PROGRAM (Options) | TIME |
|---|-------------------------|----------------------|--|-----------------|-----------|------------------|------------------|--|--------------------------|------|
| Proofing – <i>Waterproofing clean synthetics</i> . Small load 5.5 lb/2.5 kg | | | | | | | | | | 0:39 |
| | | None | Warm+/105°F/40°C | Normal | | Medium | 1 | High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | Anti-Crease | |
| Sportswear – <i>Cotton or synthetic sportswear, including microfiber and fleece</i> . Half load 6.6 lb/3 kg | | | | | | | | | | 1:07 |
| (SingleWash) (Eco) (AllergoWash) | (Pre-wash) (Soak) | Low | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Sensitive | | High | 2–3 (ExtraRinse) | High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | (SoftSteam) Anti-Crease | |
| Sneakers – <i>Non-leather sneakers</i> . 1–2 pairs | | | | | | | | | | 1:08 |
| | | High | Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Ultra-Sensitive | | Medium | 2 | Slow/600 rpm Rinse Hold No Spin | Anti-Crease | |
| Downs – <i>Down-filled items</i> . Small load 4.4 lb/2 kg | | | | | | | | | | 1:26 |
| (Eco) (AllergoWash) | (Pre-wash) | Medium | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Sensitive | | High | 3–4 (ExtraRinse) | High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | Anti-Crease | |
| Pillows – <i>Pillows with synthetic filling</i> . 1–2 pillows | | | | | | | | | | 1:28 |
| (Eco) (AllergoWash) | (Pre-wash) | Medium | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Sensitive | | High | 3–4 (ExtraRinse) | High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | Anti-Crease | |

| GENERAL (Options) | PRE-WASH → (Options) | MAIN WASH → Level Temperature | | Rhythm | (Options) | RINSE → Level | Rinses (Options) | SPIN → Speed | END PROGRAM (Options) | TIME |
|----------------------|-------------------------|----------------------------------|--|--------|-----------|------------------|------------------|-----------------|--------------------------|------|
|----------------------|-------------------------|----------------------------------|--|--------|-----------|------------------|------------------|-----------------|--------------------------|------|

Table Linens/Drapes – *Cotton or linen table clothes and drapes*. Full load 17.6 lb/8 kg

0:57

| | | | | | | | | | | |
|--|----------------------|--------|--|-----------|----------|--------|------------------|--|-------------|-------------|
| (SingleWash) (Eco) (Extra Gentle) (AllergoWash) | (Pre-wash) (Soak) | Medium | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Intensive | (Bleach) | Medium | 2–3 (ExtraRinse) | High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | (SoftSteam) | Anti-Crease |
|--|----------------------|--------|--|-----------|----------|--------|------------------|--|-------------|-------------|

Curtains – *Synthetic curtains*. Small load 4.4 lb/2 kg

1:11

| | | | | | | | | | | |
|--|-----------------|--------|---|-----------|--|-----|------------------|--|-------------|-------------|
| (Eco) (Extra Gentle) (AllergoWash) | Pre-wash | Medium | Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Sensitive | | Low | 3–4 (ExtraRinse) | Slow/600 rpm Rinse Hold No Spin | (SoftSteam) | Anti-Crease |
|--|-----------------|--------|---|-----------|--|-----|------------------|--|-------------|-------------|

Baby Clothes – *Cotton or linen baby clothes. A Cottons program*. Full load 13.2 lb/6 kg

2:26

| | | | | | | | | | | |
|--|----------------------|-----|--|-----------|----------|--------|----------------|--|-------------|-------------|
| (SingleWash) (Eco) (Extra Gentle) (AllergoWash) | (Pre-wash) (Soak) | Low | Hot+/140°F/60°C Hot/120°F/50°C Warm+/105°F/40°C Warm/85°F/30°C Cold/Tap | Intensive | (Bleach) | Medium | 3 (ExtraRinse) | Max/1600 rpm High/1200 rpm Med/800 rpm Slow/600 rpm Rinse Hold No Spin | (SoftSteam) | Anti-Crease |
|--|----------------------|-----|--|-----------|----------|--------|----------------|--|-------------|-------------|

Drain/Spin – Full load 7.6 lb/8 kg

0:01/0:12

Max/1600 rpm
High/1200 rpm
Med/800 rpm
Slow/600 rpm
No Spin

Quick Rinse – *For rinsing hand-washed items*. Full load 17.6 lb/8 kg

0:28

High 2

Max/1600 rpm
High/1200 rpm
Med/800 rpm
Slow/600 rpm
Rinse Hold
No Spin

| GENERAL (Options) | PRE-WASH → (Options) | MAIN WASH → Level Temperature | Rhythm | (Options) | RINSE → Level | Rinses (Options) | SPIN → Speed | END PROGRAM (Options) | TIME |
|----------------------|-------------------------|-------------------------------------|--------|-----------|------------------|------------------|-----------------|--------------------------|------|
|----------------------|-------------------------|-------------------------------------|--------|-----------|------------------|------------------|-----------------|--------------------------|------|

Starch – Full load 17.6 lb/8 kg

0:28

Medium

Normal

Max/1600 rpm
High/1200 rpm
Med/800 rpm
Slow/600 rpm
Rinse Hold
No Spin

Clean Machine – No load

1:19

Sanitize/170°F/75°C

Slow/600 rpm

Example sequence. Default Normal program (+ Pre-wash + Soak):

↓ Pre-wash detergent

↓ Main wash detergent

↓ Bleach

↓ Fabric softener/starch

| PRE-WASH | SOAK | MAIN WASH | SPIN DRAIN | RINSE | SPIN DRAIN | RINSE | FINAL SPIN DRAIN |
|-------------|-------------|-----------|---------------|-------|---------------|-------|---------------------|
| Tap → 105°F | | 105°F | | Tap | | Tap | 1600 rpm |
| 0:26 | 0:30 – 6:00 | 0:48 | 0:05 | 0:04 | 0:05 | 0:06 | 0:19 |

↑ UltraPhase 1
↑ UltraPhase 2

↑ Ultraphase 1
↑ UltraPhase 2
↑ Detergent/Additive Cap

↑ Fabric Care Cap

Default UltraPhase dosing:

| TEST STRIP | WATER HARDNESS | UP 1 | UP 2 |
|-------------------------|---------------------|-------|-------|
| Green Green Green Green | I <3° dH/54 ppm | 46 mL | 36 mL |
| Green Green Green Red | >4° dH/71 ppm | | |
| Green Green Red Red | II >7° dH/125 ppm | 58 mL | 45 mL |
| Green Red Red Red | III >14° dH/250 ppm | 70 mL | 54 mL |
| Red Red Red Red | >21° dH/375 ppm | | |